

**Product description**

Ultradur® B 4300 G4 FC Aqua bk15136 is suitable for plastic parts, where material approval regarding drinking water contact and direct food contact is a mandatory requirement.

The product is approved according to

- 21 CFR FDA §177.1660 "Poly(tetramethylene terephthalate)";
- European Food Contact European Food Contact Commission Regulation (EU) 10/2011;
- GMP (EC) N°2023/2006;

and suitable for drinking water contact in accordance with

- KTW-BWGL;
- WRAS (approval);
- ACS (disclosure of ingredients);
- NSF (disclosure of ingredients).

For questions regarding the compliance with further regulations, and certificates, please contact your local BASF representative or Plastics Safety (E-Mail: [plastics.safety@basf.com](mailto:plastics.safety@basf.com)).

The products can also be offered as BMBcert™ and/or Ccycled™. Due to the Massbalance approach the product properties do not change.

Abbreviated designation according to ISO 1043: PBT-GF20

**Product safety**

Ultradur® melts are stable at temperatures up to 280°C and do not give rise to hazards due to molecular degradation or the evolution of gases and vapors. Like all thermoplastic polymers, however, Ultradur decomposes on exposure to excessive thermal stresses, e.g. when it is overheated or as a result of cleaning by burning off. At temperatures of > 290 °C can be emitted: carbon monoxide, tetrahydrofuran.

Under special fire conditions traces of other toxic substances are possible. Formation of further decomposition and oxidation products depends upon the fire conditions.

When Ultradur® is properly processed and there is adequate suction at the die no risks to health are to be expected. Further safety information see safety data sheet of individual product.

Safety data sheet could be ask for at the Ultra-Infopoint under tel: 0621/60-78780.

**Physical form and storage**

Standard packaging includes the 25-kg-bag, the 1000 kg octabin (octagonal container) or the 1000 kg big bag. Other forms of packaging are possible subject to agreement. All containers are tightly sealed and should be opened only immediately prior to processing. Further precautions for preliminary treatment and drying are described in the processing section of the brochure. The bulk density is about 0,7 to 0,8g/cm<sup>3</sup>.

Ultradur® can be stored for a longer period of time in dry, well vented rooms without causing problems in processing. Ultradur® should generally have a moisture content of less than 0,04% when being processed.

In order to ensure reliable production, therefore, pre-drying should generally be the rule and the machine should be loaded via a closed conveyor system. Appropriate equipment is commercially available. Pre-drying is also for the addition of batches, e.g. in the case of inhouse pigmentation.

In order to prevent the formation of condensed water, containers stored in unheated rooms must only be opened when they have attained the temperature prevailing in the processing area. This can possibly take a very long time.

Measurements have shown that the interior of a 25-kg bag originally at 5°C had reached the temperature of 20°C in the processing area only after 48 hours.

**Note**

The data contained in this publication are based on our current knowledge and experience. In view of the many factors that may affect processing and application of our product, these data do not relieve processors from carrying out their own investigations and tests; neither do these data imply any guarantee of certain properties, nor the suitability of the product for a specific purpose. Any descriptions, drawings, photographs, data, proportions, weights etc. given herein may change without prior information and do not constitute the agreed contractual quality of the product. It is the responsibility of the recipient of our products to ensure that any proprietary rights and existing laws and legislation are observed. In order to check the availability of products please contact us or our sales agency.

## Processing Data Sheet

	Test method	Unit	Values
<b>Properties</b>			
Polymer abbreviation	-	-	<b>PBT-GF20</b>
Density	ISO 1183	kg/m <sup>3</sup>	<b>1450</b>
Melt volume rate MVR 250 °C/2.16 kg	ISO 1133	cm <sup>3</sup> /10min	<b>16</b>
<b>Drying</b>			
Moisture, max.	-	%	<b>0.04</b>
Dryer temperature <sup>1)</sup>	-	°C	<b>80 - 120</b>
Drying time	-	h	<b>4</b>
<b>Injection molding</b>			
Melt temperature range	-	°C	<b>250 - 275</b>
Melt temperature, optimal	-	°C	<b>260</b>
Mold temperature range	-	°C	<b>60 - 100</b>
Mold temperature, optimal	-	°C	<b>80</b>
<b>Machine Settings</b>			
Temperature hopper throat	-	°C	<b>80</b>
Cylinder temperature 1 (feed zone)	-	°C	<b>250</b>
Cylinder temperature 2 (compression)	-	°C	<b>255</b>
Cylinder temperature 3 (metering-zone, in front of the screw)	-	°C	<b>260</b>
Cylinder temperature 4 (nozzle)	-	°C	<b>260</b>
Peripheral screw speed	-	m/s	<b>0.25</b>
<b>Shrinkage</b>			
Molding shrinkage (parallel)	ISO 294-4	%	<b>0.40</b>
Molding shrinkage (normal)	ISO 294-4	%	<b>1.20</b>
Molding shrinkage, free, longitudinal, plate, with film gate <sup>2)</sup>	-	%	<b>0.39</b>
Molding shrinkage, free, transversal, plate with film gate <sup>2)</sup>	-	%	<b>1.28</b>

### Footnotes

1) Dry air dryer or vacuum dryer


2) Plate 150 x 150 x 3 mm, film gated

BASF SE

67056 Ludwigshafen, Germany

## Processing Data Sheet

### VISCOSITY NUMBER - RESIDENCE TIME



Unnecessarily high melt temperatures and excessively long residence times of the melt in the cylinder and the hot runner can bring about molecular degradation.

The figure shows an example (Ultradur® B4520) illustrating how the viscosity number acts as a measure of the molecular weight as a function of the melt temperature and residence time. Based on experience material degradation of less than 10 % based on the measured viscosity in solution of the granules and the molding is tolerable. In the event of values higher than this the processing and drying parameters should be checked.